

## Zone Valve Cross Reference

Model Description	Belimo Valve Body	Belimo Actuator	Honeywell	Erie	White-Rodgers	Taco
<b>18" wire lead connection, 2 way, 24V</b>						
Inverted flare, 3.5 Cv, 75 PSI close off	Z2050Q-J IF	CKQB24-S-RR	V8043G1125	VT2343G13A02A	13V16-101	Z075F2 (3/4")
1/2" sweat, 1.4 Cv, 50 PSI close off	Z2050QS-J	CKQB24-S-RR	V8043G1000	VT2212G13A02A	13S16-101	Z050C2
3/4" sweat, 5.9 Cv, 75 PSI close off	Z2075QS-K	CKQB24-S-RR	V8043G1018	VT2313G13A02A	13S16-102	Z075C2
3/4" NPT, 9.8 Cv, 75 PSI close off	Z2075Q-K	CKQB24-S-RR	V8043G1109	VT2323G13A02A	13N16-102	Z075T2
3/4" sweat, 9.8 Cv, 75 PSI close off	Z2075QS-K	CQKB24-RR	V8043C1058	VT2313G13A020	13S16-102	Z075C2
3/4" NPT, 9.8 Cv, 75 PSI close off	Z2075Q-K	CQKB24-LL	V8043D1031	VT2323G23A020	--	Z075T2
3/4" sweat, 9.8 Cv, 75 PSI close off	Z2075QS-K	CQKB24-LL	V8043D1064	VT2313G23A020	13S05-102	Z075C2
Inverted flare, 5.9 Cv 75 PSI close off	Z2050Q-J IF	CQKB24-LL	V8043D1205	VT2343G23A020	13V06-101	Z075F2 (3/4")

