

# Close-Off Pressure Globe Valve Threaded Body



	Non-Spring Return		Spring Return			Electronic Fail-Safe	
	LV	SV	LF	NF	AFB	LVK	SVK
<b>2-way</b>							
G215B(S)-C	250		160			250	
G215B(S)-F	250		160			250	
G215B(S)-G	250		160			250	
G215B(S)-J	250		160			250	
G220B(S)-J	250		155			250	
G220B(S)-K	250		155			250	
G225B(S)-K	250		147			250	
G225B(S)-L	250		147			250	
G232B(S)-M	250		141			250	
G240B(S)-N	250			250	210	250	
G250B(S)-N	250			250	120	250	
<b>3-way Mixing</b>							
G315B-G		250		250			250
G315B-J		250		250			250
G320B-K		250		250			250
G325B-L		250		179			250
G332B-M		246		133			246
G340B-N		137			167		137
G350B-N		86			105		86
<b>3-way Diverting</b>							
G315B-G		250		166			250
G315B-J		250		166			250
G320B-K		182		101			182
G325B-L		109		60			109
G332B-M		82		44			82
G340B-N		46			56		46
G350B-N		29			35		29

Tech.Doc - 4/18 - Subject to change. © Belimo Aircontrols (USA), Inc.

	Non-Spring Return		Spring Return		Electronic Fail-Safe	
	EV	RV	AF	2*AF	AVK	2*GK
<b>2-way Pressure Comp ANSI 125</b>						
G665C	140		140		140	
G680C	140		140		140	
G6100C	140			140	140	
G6125C	140			140	140	
G6150C	140			110	140	
<b>2-way Pressure Comp ANSI 125</b>						
G665CS, G665LCS	125		125		125	
G680CS, G680LCS	125		125		125	
G6100CS, G6100LCS	125			125	125	
G6125CS, G6125LCS	125			125	125	
G6150C, G6150LCS	125			125	125	
<b>2-way Pressure Comp ANSI 250</b>						
G665C-250	310		232		310	
G680C-250	310		181	310	310	
G6100C-250	310			310	310	
G6125C-250	310			241	300	
G6150C-250	310			182	232	
<b>2-way Pressure Comp ANSI 250</b>						
G665CS-250, G665LCS-250	280		232		280	
G680CS-250, G680LCS-250	280		181		280	
G6100CS-250, G6100LCS-250	280				280	
G6125CS-250, G6125LCS-250	280				280	
G6150CS-250, G6150LCS-250	280				280	280
<b>3-way ANSI 125 Mixing</b>						
G765, G765S	106	125	31	70	84	125
G780, G780S	73	125	21	48	57	102
G7100, G7100S	40	75		26		56
G7125, G7125S		47				35
G7150, G7150S		32				24
<b>3-way ANSI 250 Mixing</b>						
G765-250, G765S-250	106	198	31	70	84	149
G780-250, G780S-250	73	136	21	48	57	102
G7100-250, G7100S-250	40	75		26		56
G7125-250, G7125S-250		47				
G7150-250, G7150S-250		32				
<b>3-way ANSI 125/250 Diverting</b>						
G765D, G765DS	140		140		140	
G780D, G780DS	140		140		140	
G7100D, G7100DS	140		140		140	
G7125D, G7125DS	140			140	140	
G7150D, G7150DS	140			140		
<b>3-way ANSI 125/250 Diverting</b>						
G765DS-250	310		310		310	
G780DS-250	310		310		310	
G100DS-250	310		310		310	
G7125DS-250	310			310		
G7150DS-250	310			310		

Tech.Doc - 4/18 - Subject to change. © Belimo Aircontrols (USA), Inc.