

Type overview

Bronze Body, Stainless Steel Ball and Stem





	DN
	15
Valve size [mm]	0.5" [15]
Fluid	chilled or hot water, up to 60% glycol, steam
Fluid Temp Range (water)	-22280°F [-30138°C]
Body Pressure Rating	600 psig WOG
Close-off pressure Δps	600 psi
Flow characteristic	modified equal percentage
Max Differential Pressure (Steam)	35 psi
Flow Pattern	2-way
Leakage rate	ANSI Class VI
Controllable flow range	90° rotation
Cv	15
Maximum Inlet Pressure (Steam)	35 psi [241 kPa]
Maximum Velocity	15 FPS
Valve body	Bronze B584-C84400
Housing seal	PTFE
Stem	316 stainless steel
Stem seal	RPTFE
	Fluid Fluid Temp Range (water) Body Pressure Rating Close-off pressure Δps Flow characteristic Max Differential Pressure (Steam) Flow Pattern Leakage rate Controllable flow range Cv Maximum Inlet Pressure (Steam) Maximum Velocity Valve body Housing seal Stem

Safety notes



Suitable actuators

Seat Lock nut

Retainer

Non-Spring

Spring

Ball

Pipe connection

 WARNING: This product can expose you to lead which is known to the State of California to cause cancer and reproductive harm. For more information go to www.p65warnings.ca.gov

RPTFE

NPT

stainless steel

316 stainless steel

B16 Brass

LMB(X) GRCB(X) GRB(X)

LF



Product features

Application

This valve is typically used in air handling units on heating or cooling coils, and fan coil unit heating or cooling coils. Some other common applications include Unit Ventilators, VAV Box reheat coils and bypass loops. This valve is suitable for use in a hydronic system with variable flow.

This valve is designed with MFT functionally which facilitates the use of various control input.


Up to 35 psi steam

1/2" - 2" 600 PSIG WOG, Cold Non-Shock Federal Specification: WW-V-35C, Type II

Composition: BZ


Style: 3

Flow/Mounting details



υ	ım	ıeı	ารเ	101	าร

Туре	DN	Weight
B2050VS-15	15	0.44 lb [0.20 kg]



B2050VS..+GRC..N4

A	В	С	D	E	F
14.1" [358]	2.2" [56]	10.9" [277]	10.3" [261]	3.4" [86]	3.4" [86]



Modulating, Non-Spring Return, 24 V, Multi-Function Technology®









Toch	nical	data
ıecıı	ıııcaı	data

Electrical data	Nominal voltage	AC/DC 24 V
	Nominal voltage frequency	50/60 Hz
	Nominal voltage range	AC 19.228.8 V / DC 21.628.8 V
	Power consumption in operation	2.5 W
	Power consumption in rest position	1.2 W
	Transformer sizing	5 VA
	Electrical Connection	18 GA plenum cable, 1 m, with 1/2" conduit connector (3 m and 5 m available)
	Overload Protection	electronic throughout 095° rotation
Functional data	Operating range Y	210 V
	Operating range Y note	420 mA w/ ZG-R01 (500 Ω , 1/4 W resistor)
	Operating range Y variable	Start point 0.530 V End point 2.532 V
	Operating modes optional	variable (VDC, on/off, floating point)
	Position feedback U	210 V
	Position feedback U note	Max. 0.5 mA
	Position feedback U variable	VDC variable
	Direction of motion motor	selectable with switch 0/1
	Manual override	external push button
	Angle of rotation	Max. 95°
	Angle of rotation note	adjustable with mechanical stop
	Running Time (Motor)	150 s / 90°
	Running time motor variable	30150 s
	Noise level, motor	35 dB(A)
	Position indication	Mechanically, 3065 mm stroke
Safety data	Power source UL	Class 2 Supply
	Degree of protection IEC/EN	IP54
	Degree of protection NEMA/UL	NEMA 2
	Enclosure	UL Enclosure Type 2
	Agency Listing	cULus acc. to UL60730-1A/-2-14, CAN/CSA E60730-1:02 CE acc. to 2014/30/EU and 2014/35/EU
	Quality Standard	ISO 9001
	UL 2043 Compliant	Suitable for use in air plenums per Section
	of 2043 Compilant	300.22(C) of the NEC and Section 602 of the IMC
	Ambient humidity	Max. 95% RH, non-condensing
	Ambient temperature	-22122°F [-3050°C]
	Storage temperature	-40176°F [-4080°C]
	Storage temperature	-40176°F [-4080°C]



Technical data sheet LMX24-MFT-X1

Safety data	Servicing	maintenance-free
Weight	Weight	1.5 lb [0.70 kg]
Materials Housing material Galvanized steel and		Galvanized steel and plastic housing

Footnotes †Rated Impulse Voltage 800V, Type action 1, Control Pollution Degree 3.

Accessories

Electrical accessories	Description	Туре
	Battery backup system, for non-spring return models	NSV24 US
	Battery, 12 V, 1.2 Ah (two required)	NSV-BAT
	Feedback potentiometer 140 Ω add-on, grey	P140A GR
	Feedback potentiometer 500 Ω add-on, grey	P500A GR
	Feedback potentiometer 1 kΩ add-on, grey	P1000A GR
	Feedback potentiometer 2.8 kΩ add-on, grey	P2800A GR
	Feedback potentiometer 5 kΩ add-on, grey	P5000A GR
	Feedback potentiometer 10 kΩ add-on, grey	P10000A GR
	Auxiliary switch 1 x SPDT add-on	S1A
	Auxiliary switch 2 x SPDT add-on	S2A

Electrical installation

X INSTALLATION NOTES

(A) Actuators with appliance cables are numbered.

? Provide overload protection and disconnect as required.

Actuators may also be powered by DC 24 V.

 \mathfrak{S} Only connect common to negative (-) leg of control circuits.

 Δ A 500 Ω resistor (ZG-R01) converts the 4...20 mA control signal to 2...10 V.

Control signal may be pulsed from either the Hot (Source) or Common (Sink) 24 V line.

For triac sink the Common connection from the actuator must be connected to the Hot connection of the controller. Position feedback cannot be used with a triac sink controller; the actuator internal common reference is not compatible.


Actuators may be connected in parallel if not mechanically linked. Power consumption and input impedance must be observed.

Meets cULus requirements without the need of an electrical ground connection.


Warning! Live electrical components!

During installation, testing, servicing and troubleshooting of this product, it may be necessary to work with live electrical components. Have a qualified licensed electrician or other individual who has been properly trained in handling live electrical components perform these tasks. Failure to follow all electrical safety precautions when exposed to live electrical components could result in death or serious injury.

Wiring diagrams



Floating Point





Control mode acc. to Y,

