

Technical data

Functional data

Valve Size	3" [80]	
Fluid	chilled or hot water, up to 60% glycol	
Fluid Temp Range (water)	0250°F [-18120°C]	
Body Pressure Rating	ANSI Class 125, standard class B	
Close-off pressure Δps	175 psi	
Flow characteristic	equal percentage	
Servicing	maintenance-free	
Flow Pattern	2-way	
Leakage rate	0% for A – AB	
Controllable flow range	75°	
Cv	110	
ANSI Class	125	
Body pressure rating note	standard class B	
Cv Flow Rating	A-port: as stated in chart B-port: 70% of A – AB Cv	
Valve body	Cast iron - GG 25	
Stem seal	EPDM (lubricated)	
Seat	PTFE	
Pipe connection	pattern to mate with ANSI 125 flange	
0-ring	EPDM (lubricated)	
Ball	stainless steel	

Suitable actuators





Non-Spring

Materials

 WARNING: This product can expose you to lead which is known to the State of California to cause cancer and reproductive harm. For more information go to www.p65warnings.ca.gov

ARB(X)


Product features

Application


This valve is typically used in air handling units on heating or cooling coils, and fan coil unit heating or cooling coils. Some other common applications include Unit Ventilators, VAV box re-heat coils and bypass loops. This valve is suitable for use in a hydronic system with variable flow.




Flow/Mounting details



Upstream A Downstream AB



Dimensions





Technical data sheet B6300S-110

ARX

ARX

B

C

D

E

F

G

I

Number of Bolt Holes

16.0" [406] 6.6" [168] 16.6" [422] 11.9" [302] 3.9" [100] 3.9" [100] 6" [152] 0.7" [19]

4

ARX

A

B

C

D

E

F

G

I

Number of Bolt Holes

13.3" [338] 6.6" [168] 15.0" [380] 10.5" [267] 3.9" [100] 3.9" [100] 6" [152] 0.7" [19] 4



On/Off, Floating Point, Non-Spring Return, 24 V







a Nominal voltage	AC/DC 24 V
Nominal voltage frequency	50/60 Hz
	2.5 W
Power consumption in rest position	0.5 W
Transformer sizing	5.5 VA (class 2 power source)
Auxiliary switch	1 x SPDT, 3 A resistive (0.5 A inductive) @ AC 250 V, adjustable 0100%
Switching capacity auxiliary switch	3 A resistive (0.5 A inductive) @ AC 250 V
Electrical Connection	18 GA plenum cable with 1/2" conduit connector, degree of protection NEMA 2 / IP54, 3 ft [1 m] 10 ff [3 m] and 16ft [5 m]
Overload Protection	electronic thoughout 090° rotation
Input Impedance	600 Ω
Direction of motion motor	selectable with switch 0/1
Manual override	external push button
Angle of rotation	90°
Angle of rotation note	adjustable with mechanical stop
Running Time (Motor)	default 90 s, variable 90 or 150 s
Running time motor variable	90 or 150 s
Noise level, motor	45 dB(A)
Position indication	Mechanically, pluggable
Degree of protection IEC/EN	IP54
	NEMA 2 UL Enclosure Type 2
Agency Listing	cULus acc. to UL60730-1A/-2-14, CAN/CSA E60730-1:02, CE acc. to 2014/30/EU and 2014/35/ EU; Listed to UL 2043 - suitable for use in air plenums per Section 300.22(c) of the NEC and Section 602.2 of the IMC
Quality Standard	ISO 9001
Ambient temperature	-22122°F [-3050°C]
Storage temperature	-40176°F [-4080°C]
Ambient humidity	max. 95% r.H., non-condensing
Servicing	maintenance-free
	Power consumption in operation Power consumption in rest position Transformer sizing Auxiliary switch Switching capacity auxiliary switch Electrical Connection Overload Protection Input Impedance Direction of motion motor Manual override Angle of rotation Angle of rotation note Running Time (Motor) Running time motor variable Noise level, motor Position indication Degree of protection IEC/EN Degree of protection NEMA/UL Agency Listing Quality Standard Ambient temperature Storage temperature Ambient humidity

Safety notes

Technical data sheet ARX24-3-S



- NEMA 4X, 316L stainless steel enclosure.
- Battery Back Up System for SY(7~10)-110
- ZS-300 without brackets.
- Terminal-strip cover for NEMA 2 rating (-T models).
- MFT95 resistor kit for 4 to 20 mA control applications.
- Battery Back Up System for SY(10~12)-220P

Electrical installation

> INSTALLATION NOTES

1 Provide overload protection and disconnect as required.

2 Actuators may be connected in parallel. Power consumption and input impedance must be observed.

Actuators may also be powered by 24 VDC.

Actuators Hot wire must be connected to the control board common. Only connect common to neg. (-) leg of control circuits. Terminal models (-T) have no-feedback.

 $\frac{4}{8}$ Actuators with plenum cable do not have numbers; use color codes instead.


One built-in auxiliary switch (1x SPDT), for end position indication, interlock control, fan startup, etc.

Apply only AC line voltage or only UL-Class 2 voltage to the terminals of auxiliary switches. Mixed or combined operation of line voltage/safety extra low voltage is not allowed.


Meets cULus requirements without the need of an electrical ground connection.


Warning! Live Electrical Components!

During installation, testing, servicing and troubleshooting of this product, it may be necessary to work with live electrical components. Have a qualified licensed electrician or other individual who has been properly trained in handling live electrical components perform these tasks. Failure to follow all electrical safety precautions when exposed to live electrical components could result in death or serious injury.




On/Off






Auxiliary Switches



Floating Point



Floating Point - Triac Sink