



5-year warranty


**Technical data**

|                           |                           |   |
|---------------------------|---------------------------|---|
| <b>Functional data</b>    | Valve Size                | 2.5" [65]                                 |
|                           | Fluid                     | chilled or hot water, up to 60% glycol    |
|                           | Fluid Temp Range (water)  | 32...300°F [0...149°C]                    |
|                           | Body Pressure Rating      | ANSI Class 125, up to 175 psi below 150°F |
|                           | Flow characteristic       | linear                                    |
|                           | Servicing                 | repack/rebuild kits available             |
|                           | Rangeability Sv           | 50:1                                      |
|                           | Flow Pattern              | 3-way Diverting                           |
|                           | Leakage rate              | ANSI Class III                            |
|                           | Controllable flow range   | stem up - open AB – B                     |
|                           | Cv                        | 68  |
|                           | ANSI Class                | 125                                       |
|                           | Body pressure rating note | up to 175 psi below 150°F                 |
| <b>Materials</b>          | Valve body                | Cast iron - ASTM A126 Class B             |
|                           | Valve plug                | bronze                                    |
|                           | Stem seal                 | NLP EPDM (no lip packing)                 |
|                           | Seat                      | Stainless steel AISI 316                  |
|                           | Pipe connection           | 125 lb flanged                            |
| <b>Suitable actuators</b> | Non-Spring                | EVB(X)                                    |
|                           | Electronic fail-safe      | AVKB(X)                                   |

**Safety notes**


- **WARNING:** This product can expose you to lead which is known to the State of California to cause cancer and reproductive harm. For more information go to [www.p65warnings.ca.gov](http://www.p65warnings.ca.gov)
- The valve has been designed for use in stationary heating, ventilation and air-conditioning systems and must not be used outside the specified field of application, especially in aircraft or in any other airborne means of transport.
- Only authorised specialists may carry out installation. All applicable legal or institutional installation regulations must be complied during installation.
- The valve does not contain any parts that can be replaced or repaired by the user.
- When determining the flow rate characteristic of controlled devices, the recognised directives must be observed.

**Product features**

## Flow/Mounting details



## Dimensions


## Dimensional drawings

EVB, EVX, RVB, RVX




| A           | B          | C           | D           | E         | F         | Number of Bolt Holes |
|-------------|------------|-------------|-------------|-----------|-----------|----------------------|
| 11.7" [298] | 9.0" [229] | 25.4" [646] | 18.3" [464] | 3.6" [92] | 3.6" [92] | 4                    |

AFB, AFX




| A           | B          | C           | D           | E         | F          | Number of Bolt Holes |
|-------------|------------|-------------|-------------|-----------|------------|----------------------|
| 11.7" [298] | 9.0" [229] | 24.0" [610] | 16.9" [428] | 3.6" [92] | 5.3" [135] | 4                    |

AVKB, AVKX



| A           | B          | C           | D           | E         | F         | Number of Bolt Holes |
|-------------|------------|-------------|-------------|-----------|-----------|----------------------|
| 11.7" [298] | 9.0" [229] | 25.4" [646] | 18.3" [464] | 3.6" [92] | 3.6" [92] | 4                    |

AVKB, AVKX



| <b>A</b>    | <b>B</b>   | <b>C</b>    | <b>D</b>    | <b>E</b>  | <b>F</b>  | <b>Number of Bolt Holes</b> |
|-------------|------------|-------------|-------------|-----------|-----------|-----------------------------|
| 11.7" [298] | 9.0" [229] | 25.4" [646] | 18.3" [464] | 3.6" [92] | 3.6" [92] | 4                           |



5-year warranty



Technical data

|                        |                                    |  |
|------------------------|------------------------------------|--|
| <b>Electrical data</b> | Nominal voltage                    | AC/DC 24 V   |
|                        | Nominal voltage frequency          | 50/60 Hz   |
|                        | Power consumption in operation     | 3.5 W  |
|                        | Power consumption in rest position | 0.5 W  |
|                        | Transformer sizing                 | 6 VA (class 2 power source)  |
|                        | Electrical Connection              | 18 GA plenum cable, 3 ft [1 m], with 1/2" conduit connector, degree of protection NEMA 2 / IP54  |
|                        | Overload Protection                | electronic throughout full stroke  |
|                        | Electrical Protection              | actuators are double insulated   |
| <b>Functional data</b> | Actuating force motor              | 560 lbf [2500 N]   |
|                        | Input Impedance                    | 100 kΩ (0.1 mA), 500 Ω, 1000 Ω (on/off)  |
|                        | Position feedback U note           | No Feedback  |
|                        | Direction of motion motor          | selectable with switch 0/1   |
|                        | Manual override                    | 5 mm hex crank (3/16" Allen), supplied   |
|                        | Stroke                             | 2" [50 mm]   |
|                        | Running Time (Motor)               | 90 s, constant, independent of load  |
|                        | Running time motor note            | constant, independent of load  |
|                        | Noise level, motor                 | 60 dB(A)   |
| Position indication    | Mechanically, with pointer         |  |
| <b>Safety data</b>     | Degree of protection IEC/EN        | IP54   |
|                        | Degree of protection NEMA/UL       | NEMA 2 UL Enclosure Type 2   |
|                        | Agency Listing                     | cULus acc. to UL60730-1A/-2-14, CAN/CSA E60730-1:02, CE acc. to 2014/30/EU and 2014/35/EU; Listed to UL 2043 - suitable for use in air plenums per Section 300.22(c) of the NEC and Section 602.2 of the IMC |
|                        | Quality Standard                   | ISO 9001   |
|                        | Ambient temperature                | -22...122°F [-30...50°C]   |
|                        | Storage temperature                | -40...176°F [-40...80°C]   |
|                        | Ambient humidity                   | max. 95% r.H., non-condensing  |
|                        | Servicing                          | maintenance-free   |
|                        |                                    |  |
| <b>Weight</b>          | Weight                             | 5.73 lb [2.6 kg]   |
| <b>Materials</b>       | Housing material                   | Die cast aluminium and plastic casing  |

Safety notes



- PVC W/Shld for GV w/UGLK (GM)
- Battery Back Up System for SY(7-10)-110
- 120 to 24 VAC, 40 VA transformer.
- 50% voltage divider kit (resistors with wires).
- PC Tool computer programming interface, serial port.

**Electrical installation**

**✂ INSTALLATION NOTES**

Actuators may be connected in parallel. Power consumption and input impedance must be observed.


Actuators may also be powered by 24 VDC.

Actuators with plenum cable do not have numbers; use color codes instead.


Meets cULus requirements without the need of an electrical ground connection.

**Warning! Live Electrical Components!**


During installation, testing, servicing and troubleshooting of this product, it may be necessary to work with live electrical components. Have a qualified licensed electrician or other individual who has been properly trained in handling live electrical components perform these tasks. Failure to follow all electrical safety precautions when exposed to live electrical components could result in death or serious injury.




On/Off



Floating Point



Triac Source



Triac Sink