

**Type Overview** 

#### **Duct sensor Humidity / Temperature**

Active sensor (4...20 mA) for measuring the relative or absolute humidity and temperature in duct applications. Instead of the humidity signal, the enthalpy or the dewpoint can be selected as an output signal. IP65 / NEMA 4X rated enclosure.





Туре	utput signal a	ctive temperature	Output signal active h	umidity Probe length	
22DTH-13M	420 mA 420 mA		420 mA	140 mm	
22DTH-13Q			420 mA	270 mm	
Technical data					
Electrical data		Nominal voltage		DC 24 V	
		Nominal voltage ra	ange	DC 13.526.4 V	
		Power consumptio	n DC	1 W	
		Electrical connection	on	Pluggable spring loaded terminal block max. 2.5 mm <sup>2</sup>	
		Cable entry		Cable gland with strain relief ø68 mm	
Functional data		Application		Air	
		Multirange		4 measuring ranges selectable	
		Current output		$2x$ 420 mA, max. resistance 500 $\Omega$	
Me	asuring data	Measured values		Relative humidity Absolute humidity Dew point Enthalpies Temperature	
Specification temperature active		Sensing element to	echnology	Polymer-based capacitive sensor with stainles steel wire mesh filter	
		Measuring range t	emperature settings	Active sensor: range selectable Attention: The maximum measuring range listed does not indicate the allowable fluid temperature for the sensor. Refer to safety data for the maximum fluid temperature limits.  Setting Range [°C] Range [°F] Factory setting S0 -4060 -40160 S1 050 40140 S2 -1535 0100 S3 -2080 0200	
		Accuracy temperat	IIIA	±0.3°C @ 25°C [±0.5°F @ 77°F]	
		Long term stability		±0.05°C p.a. @ 21°C [±0.09°F p.a. @ 70°F]	
		Long term stubility			



## **Technical data**

Specification Humidity	Sensing element technology	Polymer-based capacitive sensor with stainless steel wire mesh filter
	Measuring range	0100% RH
	Measuring range absolute humidity	adjustable at the transducer: 050 g/m³ (default setting) 080 g/m³
	Measuring range enthalpy	085 kJ/kg
	Measuring range dew point	adjustable at the transducer: 050°C [40140°F] (default setting) -2080°C [0200°F]
	Accuracy	±2% between 080% RH @ 25°C
	Long term stability	±0.3% RH p.a. @ 21°C @ 50% RH
	Time constant $\tau$ (63%) in the air duct	Typical 10 s @ 3 m/s
Safety data	Protection class IEC/EN	III, Safety Extra-Low Voltage (SELV)
	Power source UL	Class 2 Supply
	Degree of protection IEC/EN	IP65
	Degree of protection NEMA/UL	NEMA 4X
	EU Conformity	CE Marking
	Certification IEC/EN	IEC/EN 60730-1
	Quality Standard	ISO 9001
	UL Approval	cULus acc. to UL60730-1A/-2-9/-2-13, CAN/CSA E60730-1/-2-9
	Type of action	Type 1
	Rated impulse voltage supply	0.8 kV
	Pollution degree	3
	Ambient humidity	Max. 95% RH, non-condensing
	Ambient temperature	-3550°C [-30120°F]
	Fluid humidity	0100% RH, short-term condensation permitted
	Fluid temperature	-4080°C [-40175°F]
	Operating condition airflow	max. 12 m/s
Materials	Housing	Cover: PC, orange Bottom: PC, orange Seal: NBR70, black UV resistant
	Cable gland	PA6, black
	·	

# Safety notes



This device has been designed for use in stationary heating, ventilation and air-conditioning systems and must not be used outside the specified field of application. Unauthorised modifications are prohibited. The product must not be used in relation with any equipment that in case of a failure may threaten humans, animals or assets.

Ensure all power is disconnected before installing. Do not connect to live/operating equipment.

Only authorised specialists may carry out installation. All applicable legal or institutional installation regulations must be complied with during installation.

The device contains electrical and electronic components and must not be disposed of as household refuse. All locally valid regulations and requirements must be observed.



#### Remarks

#### General remarks concerning sensors

Sensing devices with a transducer should always be operated in the middle of the measuring range to avoid deviations at the measuring end points. The ambient temperature of transducer electronics should be kept constant. The transducers must be operated at a constant supply voltage ( $\pm 0.2$  V). When switching the supply voltage on/off, onsite power surges must be avoided.

Remark: Occurring draft leads to a better carrying-off of dissipative power at the sensor. Thus temporally limited fluctuations might occur upon temperature measurement.

# Build-up of self-heating by electrical dissipative power

Temperature sensors with electronic components always have a dissipative power which affects the temperature measurement of the ambient air. The dissipation in active temperature sensors shows a linear increase with rising operating voltage. The dissipative power should be taken into account when measuring temperature.

In case of a fixed operating voltage ( $\pm 0.2$  V), this is normally done by adding or reducing a constant offset value. As Belimo transducers work with a variable operating voltage, for reasons of production engineering only one operating voltage can be taken into consideration. Transducers 0...10 V / 4...20 mA have a standard setting at an operating voltage of DC 24 V. This means that at this voltage, the expected measuring error of the output signal will be the least. For other operating voltages, the offset error will be increased by a changing power loss of the sensor electronics.

If a readjustment directly at the active sensor should be necessary during later operation, this can be done with the following adjustment methods.

- For sensors with NFC or dongle with the corresponding Belimo app
- For sensors with a trimming potentiometer on the sensor board
- For bus sensors via bus interface with a corresponding software variable

#### Application notice for humidity sensors

The humidity sensor is extremely sensitive. Touching the sensor element or exposing it to aggressive substances like chlorine, ozone, ammonia, hydrogen peroxide or ethanol (i.e. as a cleaning agent) may affect the measurement accuracy.

Long term operation outside the recommended conditions (5...60°C and 20...80% RH) can result in a temporary offset. After returning into the recommended range, this effect disappears.

### Parts included

Description	Туре
Mounting flange for duct sensor 19.5 mm, up to max. 120°C [248°F],	A-22D-A35
Plastic	


#### **Accessories**

Optional accessories	Description	Туре	
	Replacement filter sensor probe tip, wire mesh, Stainless steel	A-22D-A06	
	Connection adapter flex conduit, M20x1.5, for cable gland 1x 6 mm,	A-22G-A01.1	


Multipack 10 pcs.



## Wiring diagram



① Status LED
RH Relative humidity
absH Absolute humidity
EntH Enthalpy
TPkt/Dew Dew point
(Measured value available on output
AOI1)




Correct temperature values are only available, when the humidity output AOI1 and both inputs UB + are connected.


The following measuring ranges can be adjusted through the jumper settings:

Setting	Range [°C]	Range [°F]	Factory setting
S0	-4060	-40160	
S1	050	40140	
S2	-1535	0100	
S3	-2080	0200	



# **Dimensions**





L = Probe length

Туре	Probe length	Weight
22DTH-13M	140 mm	0.14 kg
22DTH-13Q	270 mm	0.20 kg

# **Further documentation**

• Installation instructions