

Outdoor sensor with weather and radiated heat shield Humidity / Temperature

Active humidity and temperature sensor (0...10 V) for outside applications. The radiation shield protects the outside sensors from rain and radiated heat. With the curved shape and colour of the plates airflow is able to move across the sensors to keep radiated temperatures from rooftops and surrounding surfaces from affecting humidity readings.



### Type Overview

| Type       | Output signal active temperature | Output signal active humidity |
|------------|----------------------------------|-------------------------------|
| 22UTH-110X | 0...5 V, 0...10 V                | 0...5 V, 0...10 V             |

### Technical data

| <b>Electrical data</b>            | Nominal voltage                           | AC/DC 24 V   |   |                 |            |            |                 |    |          |           |  |    |        |          |  |    |          |         |  |    |          |         |
|-----------------------------------|---|--|---|-----------------|------------|------------|-----------------|----|----------|-----------|--|----|--------|----------|--|----|----------|---------|--|----|----------|---------|
|                                   | Nominal voltage range                     | AC 21.6...26.4 V / DC 13.5...26.4 V  |   |                 |            |            |                 |    |          |           |  |    |        |          |  |    |          |         |  |    |          |         |
|                                   | Power consumption AC                      | 0.8 VA   |   |                 |            |            |                 |    |          |           |  |    |        |          |  |    |          |         |  |    |          |         |
|                                   | Power consumption DC                      | 0.4 W  |   |                 |            |            |                 |    |          |           |  |    |        |          |  |    |          |         |  |    |          |         |
|                                   | Electrical connection                     | Pluggable spring loaded terminal block max. 2.5 mm <sup>2</sup>                  |   |                 |            |            |                 |    |          |           |  |    |        |          |  |    |          |         |  |    |          |         |
|                                   | Cable entry                               | Cable gland with strain relief ø6...8 mm   |   |                 |            |            |                 |    |          |           |  |    |        |          |  |    |          |         |  |    |          |         |
| <b>Functional data</b>            | Application                               | Air  |   |                 |            |            |                 |    |          |           |  |    |        |          |  |    |          |         |  |    |          |         |
|                                   | Multirange                                | 4 measuring ranges selectable  |   |                 |            |            |                 |    |          |           |  |    |        |          |  |    |          |         |  |    |          |         |
|                                   | Voltage output                            | 2 x 0...5 V, 0...10 V, min. resistance 10 kΩ                                     |   |                 |            |            |                 |    |          |           |  |    |        |          |  |    |          |         |  |    |          |         |
|                                   | Output signal active note                 | Output 0...5/10 V with Jumper adjustable   |   |                 |            |            |                 |    |          |           |  |    |        |          |  |    |          |         |  |    |          |         |
| <b>Measuring data</b>             | Measured values                           | Relative humidity<br>Absolute humidity<br>Dew point<br>Enthalpies<br>Temperature |   |                 |            |            |                 |    |          |           |  |    |        |          |  |    |          |         |  |    |          |         |
|                                   | <b>Specification temperature active</b>   | Sensing element technology   | Polymer-based capacitive sensor with stainless steel wire mesh filter   |                 |            |            |                 |    |          |           |  |    |        |          |  |    |          |         |  |    |          |         |
|                                   |   | Measuring range temperature settings   | Active sensor: range selectable<br>Attention: The maximum measuring range listed does not indicate the allowable fluid temperature for the sensor. Refer to safety data for the maximum fluid temperature limits.<br><table border="1"> <thead> <tr> <th>Setting</th> <th>Range [°C]</th> <th>Range [°F]</th> <th>Factory setting</th> </tr> </thead> <tbody> <tr> <td>S0</td> <td>-40...60</td> <td>-40...160</td> <td></td> </tr> <tr> <td>S1</td> <td>0...50</td> <td>40...140</td> <td></td> </tr> <tr> <td>S2</td> <td>-15...35</td> <td>0...100</td> <td></td> </tr> <tr> <td>S3</td> <td>-20...80</td> <td>0...200</td> <td>✓</td> </tr> </tbody> </table> | Setting         | Range [°C] | Range [°F] | Factory setting | S0 | -40...60 | -40...160 |  | S1 | 0...50 | 40...140 |  | S2 | -15...35 | 0...100 |  | S3 | -20...80 | 0...200 |
|                                   | Setting                                   | Range [°C]   | Range [°F]  | Factory setting |            |            |                 |    |          |           |  |    |        |          |  |    |          |         |  |    |          |         |
|                                   | S0  | -40...60   | -40...160   |                 |            |            |                 |    |          |           |  |    |        |          |  |    |          |         |  |    |          |         |
| S1                                | 0...50                                    | 40...140   |   |                 |            |            |                 |    |          |           |  |    |        |          |  |    |          |         |  |    |          |         |
| S2                                | -15...35                                  | 0...100  |   |                 |            |            |                 |    |          |           |  |    |        |          |  |    |          |         |  |    |          |         |
| S3                                | -20...80                                  | 0...200  | ✓   |                 |            |            |                 |    |          |           |  |    |        |          |  |    |          |         |  |    |          |         |
| Accuracy temperature              | ±0.3°C @ 25°C [±0.5°F @ 77°F]             |  |   |                 |            |            |                 |    |          |           |  |    |        |          |  |    |          |         |  |    |          |         |
| Long term stability               | ±0.05°C p.a. @ 21°C [±0.09°F p.a. @ 70°F] |  |   |                 |            |            |                 |    |          |           |  |    |        |          |  |    |          |         |  |    |          |         |
| Time constant τ (63%) in the room | Typical 351 s @ 0 m/s                     |  |   |                 |            |            |                 |    |          |           |  |    |        |          |  |    |          |         |  |    |          |         |

**Technical data**

|                               |  |   |                                      |
|-------------------------------|--|---|--------------------------------------|
| <b>Specification Humidity</b> | Sensing element technology             | Polymer-based capacitive sensor with stainless steel wire mesh filter                                 |                                      |
|                               | Measuring range                        | 0...100% RH non-condensing  |                                      |
|                               | Measuring range absolute humidity      | adjustable at the transducer:<br>0...50 g/m <sup>3</sup> (default setting)<br>0...80 g/m <sup>3</sup> |                                      |
|                               | Measuring range enthalpy               | 0...85 kJ/kg  |                                      |
|                               | Measuring range dew point              | adjustable at the transducer:<br>0...50°C [40...140°F] (default setting)<br>-20...80°C [0...200°F]    |                                      |
|                               | Accuracy                               | ±2% between 0...80% RH @ 25°C   |                                      |
|                               | Long term stability                    | ±0.3% RH p.a. @ 21°C @ 50% RH   |                                      |
|                               | Time constant $\tau$ (63%) in the room | Typical 16 s @ 0 m/s  |                                      |
|                               | <b>Safety data</b>                     | Protection class IEC/EN   | III, Safety Extra-Low Voltage (SELV) |
|                               |  | Power source UL   | Class 2 Supply                       |
| Degree of protection IEC/EN   |  | IP65  |                                      |
| Degree of protection NEMA/UL  |  | NEMA 4X   |                                      |
| Housing                       |  | UL Enclosure Type 4X  |                                      |
| EU Conformity                 |  | CE Marking  |                                      |
| Certification IEC/EN          |  | IEC/EN 60730-1  |                                      |
| Quality Standard              |  | ISO 9001  |                                      |
| Type of action                |  | Type 1  |                                      |
| Rated impulse voltage supply  |  | 0.8 kV  |                                      |
| Pollution degree              |  | 3   |                                      |
| Ambient humidity              |  | Short-term condensation permitted   |                                      |
| Ambient temperature           |  | -35...50°C [-30...120°F]  |                                      |
| Fluid humidity                |  | Short-term condensation permitted   |                                      |
| Fluid temperature             |  | -35...50°C [-30...122°F]  |                                      |
| Operating condition airflow   | max. 12 m/s                            |   |                                      |
| <b>Materials</b>              | Housing                                | Cover: PC, white<br>Bottom: PC, white<br>Seal: NBR70, black<br>UV resistant                           |                                      |
|                               | Cable gland                            | PA6, white  |                                      |

**Safety notes**


This device has been designed for use in stationary heating, ventilation and air-conditioning systems and must not be used outside the specified field of application. Unauthorised modifications are prohibited. The product must not be used in relation with any equipment that in case of a failure may threaten humans, animals or assets.

Ensure all power is disconnected before installing. Do not connect to live/operating equipment.

Only authorised specialists may carry out installation. All applicable legal or institutional installation regulations must be complied with during installation.

The device contains electrical and electronic components and must not be disposed of as household refuse. All locally valid regulations and requirements must be observed.

Remarks

- General remarks concerning sensors** When using lengthy connection wires (depending on the cross section used) the measuring result might be falsified due to a voltage drop at the common GND-wire (caused by the voltage current and the line resistance). In this case, 2 GND-wires must be wired to the sensor - one for supply voltage and one for the measuring current.
- Sensing devices with a transducer should always be operated in the middle of the measuring range to avoid deviations at the measuring end points. The ambient temperature of transducer electronics should be kept constant. The transducers must be operated at a constant supply voltage ( $\pm 0.2$  V). When switching the supply voltage on/off, onsite power surges must be avoided.
- Remark: Occurring draft leads to a better carrying-off of dissipative power at the sensor. Thus temporally limited fluctuations might occur upon temperature measurement.**
- Build-up of self-heating by electrical dissipative power** Temperature sensors with electronic components always have a dissipative power which affects the temperature measurement of the ambient air. The dissipation in active temperature sensors shows a linear increase with rising operating voltage. The dissipative power should be taken into account when measuring temperature.
- In case of a fixed operating voltage ( $\pm 0.2$  V), this is normally done by adding or reducing a constant offset value. As Belimo transducers work with a variable operating voltage, for reasons of production engineering only one operating voltage can be taken into consideration. Transducers 0...10 V / 4...20 mA have a standard setting at an operating voltage of DC 24 V. This means that at this voltage, the expected measuring error of the output signal will be the least. For other operating voltages, the offset error will be increased by a changing power loss of the sensor electronics.
- If a readjustment directly at the active sensor should be necessary during later operation, this can be done with the following adjustment methods.
- For sensors with NFC or dongle with the corresponding Belimo app
  - For sensors with a trimming potentiometer on the sensor board
  - For bus sensors via bus interface with a corresponding software variable
- Application notice for humidity sensors** The humidity sensor is extremely sensitive. Touching the sensor element or exposing it to aggressive substances like chlorine, ozone, ammonia, hydrogen peroxide or ethanol (i.e. as a cleaning agent) may affect the measurement accuracy.
- Long term operation outside the recommended conditions (5...60°C and 20...80% RH) can result in a temporary offset. After returning into the recommended range, this effect disappears.


Parts included

- Dowels
- Screws

Accessories


| Optional accessories | Description   | Type      |
|----------------------|---|-----------|
|                      | Replacement filter sensor probe tip, wire mesh, Stainless steel | A-22D-A06 |

Wiring diagram



2 x 0...5/10 V


- ① Status LED
- RH Relative humidity
- absH Absolute humidity
- Enth Enthalpy
- TPkt/Dew Dew point
- (Measured value available on output AOU1)



The following measuring ranges can be adjusted through the jumper settings:

| Setting | Range [°C] | Range [°F] | Factory setting |
|---------|------------|------------|-----------------|
| S0      | -40...60   | -40...160  |                 |
| S1      | 0...50     | 40...140   |                 |
| S2      | -15...35   | 0...100    |                 |
| S3      | -20...80   | 0...200    | ✓               |

Dimensions



Type

22UTH-110X

Weight

0.54 kg

Further documentation

- Installation instructions