

Stem heater for valves DN 65...250

- for valves H6..N / H6..R / H7..N / H7..R / H7..W..-S7
- for temperatures down to -10° C



### Technical data

<b>Electrical data</b>	Nominal voltage	AC/DC 24 V
	Nominal voltage frequency	50/60 Hz
	Power consumption heating	60 W
	Connection supply	Cable 1 m
<b>Functional data</b>	Fluid temperature	-10...20°C [14...68°F]
<b>Safety data</b>	Degree of protection IEC/EN	IP40
	Certification IEC/EN	IEC/EN 60529
	Ambient temperature	-10...40°C [14...104°F]
	Servicing	maintenance-free
<b>Weight</b>	Weight	0.055 kg

### Safety notes



- This device has been designed for use in stationary heating, ventilation and air-conditioning systems and must not be used outside the specified field of application, especially in aircraft or in any other airborne means of transport.
- Only authorised specialists may carry out installation. All applicable legal or institutional installation regulations must be complied with during installation.
- The device contains electrical and electronic components and must not be disposed of as household refuse. All locally valid regulations and requirements must be observed.

### Product features

**Used materials** Foam